



## VH-Z20W

Ultra Small High-performance Zoom Lens (20-200X)

\*Please note that accessories depicted in the image are for illustrative purposes only and may not be included with the product.

This model has been discontinued.
Contact Us: 1-888-539-3623
Compliance with the certification standard is ensured as of the time of shipment from our company.

Recommended Replaceable Products: <u>Ultra-small</u>, <u>high-performance zoom lens (20 x to 200 x) - VH-Z20T</u>

## **Specifications**

Model		VH-Z20W
Magnification		20×, 30×, 50×, 100×, 150×, 200×*1
Field-of-view	Horizontal	15.24 mm0.60" (20x) 10.16 mm0.40" (30x) 6.10 mm0.240" (50x) 3.05 mm0.12" (100x) 2.03 mm0.080" (150x) 1.52 mm0.060" (200x)*1
	Vertical	11.40 mm0.45" (20x) 7.60 mm0.299" (30x) 4.56 mm0.18" (50x) 2.28 mm0.09" (100x) 1.52 mm0.060" (150x) 1.14 mm0.04" (200x)*1
	Diagonal	19.05 mm0.75" (20x) 12.70 mm0.50" (30x) 7.62 mm0.300" (50x) 3.81 mm0.15" (100x) 2.54 mm0.10" (150x) 1.91 mm0.075" (200x)*1
Depth-of-field		34 mm1.34" (20x) 15.5 mm0.61" (30x) 6.0 mm0.236" (50x) 1.6 mm0.063" (100x) 0.74 mm0.03" (150x) 0.44 mm0.02" (200x)*1*2
Working distance		25.5 mm1.00"*1

<sup>\*1</sup> Magnification on a 15-inch monitor

The depth-of-field changes depending on the setting of the aperture.

KEYENCE AMERICA 1-888-539-3623(Toll Free) https://www.keyence.com 2024/12/16 Page 1 of 1

<sup>\*2</sup> The value when the lens is set with priority to depth-of-field.